



PMK Under Desk Instructions



Every module includes a spare fuse

Thank you for purchasing ABL's PMK power module unit. PMK has been manufactured and tested in accordance with relevant British Standards. This will enable the requirements of BS6396:2008 to be met (if installed and tested as specified in the standard) Once installed and tested, any modifications should be carried out by a competent person. USE: This power module is designed for use in office and educational establishments only.

The individual fuse rating for each socket will be a maximum of 5A as specified on the product, any item of equipment rated in excess of 5 Amp, MUST have a separate power supply, therefore items such as Vacuum Cleaners, Kettles, Coffee Makers, and Fan Heaters should not be connected via these power modules. FUSES: The fuses in the product are ceramic 5mm x 20mm either 3.15A or 5A rated. Should replacements be required please contact the company that supplied this product. FIXING: Use only the fixings shown in the leaflet to mount this product.

CONNECTION: Using the mains extension lead that may be supplied, connect this into the short tail lead on the rear of the product. If included in this product also plug the other connection leads into the sockets on the rear of the product (ensure the Non Booted end is plugged into the product) should you need to re-site this product and require shorter or longer leads, simply replace the leads supplied with the appropriate length leads which can be obtained from the supplier of the product.