

# Combination Units

## Recessed



- Saves water
- Save space
- Cuts bullying
- Reduces vandalism
- Clear sight lines

### Ideal for:

- Schools
- Colleges
- Public facilities

### BC 30 SCA Dolphin Touch Free Wash Station

- The Dolphin Wash Station provides a complete hand washing facility at the point of use. An ideal solution where space is at a premium.
- Unit automatically dispenses a measured amount of liquid soap. After a time delay allowing the user to lather hands a measured amount of temperature controlled water is dispensed. Finally the integral warm air dryer is activated to dry hands.
- All functions are adjustable
- Finished in satin stainless steel
- 13A fused spur 220/240v single phase electrical supply (50hz)
- A single 15mm cold water feed (3/4" BSP)
- Includes an integral water heater
- Ø32mm plastic waste pipe connection
- 3 core 1.5mm cables
- 1 bar minimum water pressure required at a minimum static pressure of 1.0 - 7.0 bar
- Soap level indicator warns of low soap, allowing 75 further shots before the unit is deactivated
- CE approved product

- IP21 protection
- 12 months manufacturer's warranty
- Suitable for duct accessible applications soap reservoir may be filled from both sides of the unit
- **This wash station is also available as a surface mounted option – please enquire**
- **WRAS approved**



### Product Data

- H 257 x W 340 mm
- Recess dimensions : H 790-798 W 397-405  
D minimum of 105mm
- Projection 76mm
- Weight: 19.7kg
- Power consumption 2.5Kw –3.1Kw
- Soap specification 1-600cst (0.85SG)



### Related items



**DB 1650**  
page 176



**BC 194**  
page 39



**BC 708**  
page 115



**BC 2200SA(R)**  
page 160



**BC 800R**  
page 84



**BC 22SCA**  
page 145



### BC 30SCA Dolphin Automatic Wash Station

#### Key facts:



- Recess depth – minimum 105mm
- Built in water heater
- Excellent water saving device – as little as 0.5 litre per wash
- Vandal resistant
- Full instruction manual



# Combination Units



Combination Units



All dimensions in mm

Mounting heights guide, see pages 316-325