

Surface Protection - Product Code: Stainless Steel Waste Bins KWB900




Product Specification:



- Suitable for cleanroom, sterile rooms, food processing and research areas
- No dirt traps
- Doors are fitted with budget locks or ball locks
- Left or right hand hinges available
- Unique fully concealed hinge system
- Various handles available including D handles and spring loaded recessed handles.

Product Dimensions:

Reference	Height	Width	Depth
KWB900	900mm	800mm	430mm
KWB500	500mm	400mm	450mm



Options:

Stainless Steel Grade	Finish	Thickness	Lock	Hinge
304	Satin Finish 320 Grit Polished	2mm	Budget	Right Hand Side
316	Electropolished	3mm	Ball Catch	Left Hand Side
	Bead Blasted		Other	
	Bead Blasted & Electropolished			
	320 grit polished & Electropolished			
	Powder Coated			

Overview:

The Kent Stainless waste bins are designed for use in gowning/changing rooms where it is imperative no contained operators or equipment enter the cleanroom area.

The freestanding waste bins ensure operators have a clean, low maintenance unit in which to discard unwanted garments and / or waste. Available in single or double units.

Maintenance:

Stainless Steel:

Clean the stainless steel components using warm water with a mild detergent with a non abrasive cloth or sponge. Heavier stains may require the use of a nylon scouring pad or a stainless steel cleaner. To remove paint or graffiti (or light concrete splashes) use a cloth and alkaline or solvent paint strippers according to type of paint.

For Satin Finish Stainless try to follow the direction of the grain when cleaning vigorously or polishing. For Bead Blasted Finish use a circular motion.

Rust spots or 'tea stains' can occur on the surface of the material, these are normally caused by contamination from ordinary mild steel, particularly in areas where construction work has been undertaken.

Where contamination of the stainless has occurred from ordinary mild steel coming into contact with the stainless, use Rust Remover 410. In cases where the surface is severely stained as a result of severe environmental conditions or scratched due to misuse, it may still be possible to restore the original finish using chemicals such as Oxalic Acid solution. There are many stainless steel polishes available to enhance the surface finish. We recommend [Mister Stainless Ltd.](#) as a provider for stainless steel cleaning products